


Broadcast Tools® HR-1

Headphone Remote

Calculating the Maximum Amplifier Load

Minimum impedance is 8 ohms for the headphone outputs of the HPA-4 Headphone Amplifier. For figuring headphone impedances, see the table at right. Include in your calculations the headphones connected to the front or rear jacks of the HPA-4 and the headphones connected to the corresponding jacks.



HR-1 Features

- Makes headphone amp outputs available at a remote location.
- Provides level control for an individual output as well as a Loop Through Output. This output provides line level audio that is not affected by the HR-1's gain control.
- Offers a variety of mounting options.

How many Headphones of various impedances may be used with each Output of the HPA-4.

Impedance of Headphones	Maximum Number/Channel
24	3
32	4
100	10
200	20
400	40
600	60



Flush mount into furniture (w/ HR-1/MP-XLR option). Connector not included. XLR hole compatible with the Switchcraft D3F and Neutrik NC3FP-1 connectors.



Flush mount into furniture (w/ HR-1/MP option).



Mount to top or underside of desk or cabinet.

131 State Street, Sedro-Woolley, WA 98284 • 360.854.9559 • Fax 360.854.9479

Visit us online at www.broadcasttools.com

Copyright © 1989-2006 by Broadcast Tools, Inc. All Rights Reserved.